

Product data sheet

Characteristics

QOXD320

Mini CB, QO, 20 A, 3P, 240/415 V, 3 kA, Plug in

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 248.00 USD



Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	240/415 V AC
Mounting Type	Plug-in
Number of Poles	3P
Circuit Breaker Type	Standard
Ratings	Not rated
Electrical Connection	Pressure plate

Complementary

Interrupt Rating	3 kA Icu per: IEC 947-2 at: 240/415 V AC 50/60 Hz
Number of Panel Spaces	3
Height	3 in
Depth	2.91 in
Width	2.23 in

Environment

Certifications	IEC
Ambient Rating	104 °F (40 °C)

Ordering and shipping details

Category	00920 - QO INTERNATIONAL SENA
Discount Schedule	DE2A
GTIN	00785901826118
Nbr. of units in pkg.	1

Package weight(Lbs)	0.8499999999999998
Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------