

Product availability : Stock - Normally stocked in distribution facility



Price* : 4,065.00 USD



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	400 A
Short-circuit current	25 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface Semi flush field installed flange kit
Number of spaces	8
Number of circuits	16
Mounting	Surface Semi-flush with field installed flange kit
Number of Tandem Breakers	8
Hub type	A-L
Electrical connection	Studs line side Feed-thru lugs service ground
Wire Size	AWG 4...250 kcmil (aluminium) service ground AWG 4...250 kcmil (copper) service ground
Disconnect	Service disconnect (factory installed)
Main Breaker Rating	200 A
Branch Breaker Rating	200 A
Service feed location	UG
Bypass type	Class 320 lever bypass
Depth	7.87 in
Width	28.25 in
Height	43 in

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Product certifications	UL E-6294
------------------------	-----------

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901429845
Nbr. of units in pkg.	1
Package weight(Lbs)	115
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------