





MINIATURE CIRCUIT BREAKER 277V 20A

QYU120

- Discontinued on: Dec 8, 2020
- ! End-of-service on: Dec 31, 2020

! Discontinued

Main

Product	Supplementary Protector
Range	QYU
Circuit Breaker Type	Standard

Complementary

Current Rating	20 A
Voltage Rating	277 V AC
Mounting Type	Unit mount
Number Of Poles	1P
Short Circuit Current Rating	5 kA
Electrical Connection	Lugs
Wire Size	AWG 14AWG 2 aluminium/copper
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 14AWG 2)

Environment

Certifications UL Recognized

Ordering and shipping details

Category	00900-QOU BREAKERS & SWITCH
Discount Schedule	DE2
Gtin	00785901586661
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.90 in (2.286 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	3.10 in (7.874 cm)
Package 1 Weight	5.76 oz (163.293 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Contractual warranty

Warranty

18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
②	Halogen Free Product

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration