



Price\* : 1,419.00 USD



ⓘ Discontinued

RC12L200CH has not been replaced. Please contact your customer care center for more information.

### Main

Product or component type	Meter Mains
Range of product	Homeline

### Complementary

Line Rated Current	200 A
Short-circuit current	10 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface
Number of spaces	0
Number of circuits	0
Mounting	Surface
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil (aluminium/copper) line side AWG 12...AWG 2/0 (aluminium/copper) service ground
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	Horn bypass
Depth	6.1 in
Width	14.89 in
Height	26.16 in

### Environment

Product certifications	UL E-6294
------------------------	-----------

## Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901001041
Nbr. of units in pkg.	1
Package weight(Lbs)	11
Returnability	Y
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------