



Main

Range of product	Zelio Time
Product or component type	Electromechanical timing relay
Discrete output type	Relay
Contacts type and composition	1 NO instantaneous contact
Component name	RE88226
Time delay type	Function 2 Function 3 Function 4
Time delay range	0...12 min
[Us] rated supply voltage	220...240 V AC 50 Hz
Electrical connection	Screw-clamp terminals 1 x 0.5...2 x 2.5 mm ²
Nominal output current	5 A

Complementary

Voltage range	0.8...1 Un 131 °F (55 °C) IEC 60255-100
Repeat accuracy	+/- 1.5 % 0...12 min +/- 1.5 % 0...60 s +/- 4 % 0...6 s
Setting accuracy of time delay	+/- 2 % 0...12 min +/- 5 % 0...6 s
Reset time	0.2 s
On-load factor	100 %
Power consumption in VA	3 VA 0.8
[Ui] rated insulation voltage	380 V AC VDE 0110 group C 440 V DC VDE 0110 group C
[Ith] conventional free air thermal current	6.3 A
Breaking capacity	5 A 230 V 0.41 10000 cycles
Fixing mode	Plug-in 8-pin socket
Net weight	0.41 lb(US) (0.185 kg)

Environment

Standards	IEC 60529
-----------	-----------

VDE 0660
VDE 0435
VDE 0110
NF C 45250

Product certifications	CSA UR
Ambient air temperature for storage	-4...158 °F (-20...70 °C)
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Environmental characteristic	Tropical environment IEC 60068-2-10 Standard environment
IP degree of protection	IP10 terminal block) IP40 enclosure)
Vibration resistance	4 gn 10...55 Hz)
Dielectric test voltage	2 kV IEC 60255-5 2 kV VDE 0435

Ordering and shipping details

GTIN	03389110279900
Package weight(Lbs)	0.46 lb(US) (0.210 kg)

Contractual warranty

Warranty	18 months
----------	-----------