

RGA36100CU43A

MOLDED CASE CIRCUIT BREAKER 600V 1000A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 36,581.00 USD



Main

Product or component type	Circuit breaker
Range of product	PowerPact R
Current sensor rating range	1000 A
Trip unit technology	Electronic ammeter Micrologic 5.0 A LSI

Complementary

[Ie] rated operational current	1000 A
System Voltage	600 V AC
Mounting mode	I-Line
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Breaking capacity code	G
Continuous current rating	100 %
Electrical connection	I-Line connection line Lugs load
AWG gauge	AWG 3/0...600 kcmil aluminium/copper
Height	13.38 in
Width	14.96 in
Depth	13.78 in

Environment

Product certifications	CSA IEC UL listed
------------------------	-------------------------

Ordering and shipping details

Category	01240 - RG,H,J,K,L,N I-LINE BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	52
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------