

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 25,511.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact R
Current sensor rating range	800 A
Trip unit technology	Electronic ammeter Micrologic 5.0 A LSI

### Complementary

[Ie] rated operational current	800 A
System Voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 35 kA 480 V AC 18 kA 600 V AC
Breaking capacity code	G
Continuous current rating	80 %
Electrical connection	Busbar connection load Busbar connection line
Height	16.24 in
Width	16.53 in
Depth	14.49 in

### Environment

Product certifications	IEC UL listed CSA
------------------------	-------------------------

### Ordering and shipping details

Category	01245 - RG,H,J,K,L,N UNIT MT BREAKERS
----------	---------------------------------------

Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	52
Returnability	Y
Country of origin	US

**Offer Sustainability**

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------