

# RKF36200U64AE1

## MOLDED CASE CIRCUIT BREAKER 600V 2000A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 32,180.00 USD



### Main

Product or component type	Circuit breaker
Range of product	PowerPact R
Trip unit technology	Electronic power Micrologic 6.0 P LSIG

### Complementary

[Ie] rated operational current	2000 A
System Voltage	600 V AC
Mounting mode	Unit mount
Poles description	3P
Breaking capacity	65 kA 240 V AC 65 kA 480 V AC 65 kA 600 V AC
Continuous current rating	80 %
Electrical connection	Busbar connection load Busbar connection line
Height	16.24 in
Width	16.53 in
Depth	14.49 in
Communication interface	Modbus
Tightening torque	68 N.m for 50...400 mm <sup>2</sup> (AWG 1/0...750 kcmil) 68 N.m for 50...150 mm <sup>2</sup> (AWG 1/0...300 kcmil)

### Environment

Product certifications	IEC CSA UL listed
------------------------	-------------------------

## Ordering and shipping details

Category	01245 - RG,H,J,K,L,N UNIT MT BREAKERS
Discount Schedule	DE2
Nbr. of units in pkg.	1
Package weight(Lbs)	74
Returnability	Y
Country of origin	US

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP, which is known to the State of California to cause cancer, and
----- Substance 2	DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------