

Product data sheet

Specifications



REACTOR DRIVE LINE 3PH 1HP 5% 460V T-1

RL00212

⚠ Discontinued on: Dec 2, 2020

⚠ End-of-service on: Dec 31, 2020

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Complementary

Line Rated Current	2 A
Awg Gauge	AWG 22...AWG 14
Depth	6 in (152.40 mm)
Electrical Connection	Screw clamp terminal
Height	8 in (203.20 mm)
Permissible Voltage	600 V AC
Net Weight	11 lb(US) (4.99 kg)
Protection Type	Harmonic distortion Current protection Overvoltage protection
Width	8 in (203.20 mm)

Environment

Product Certifications	UL listed file E180243 CE CSA LR29753
------------------------	---

Ordering and shipping details

Category	US1CP4C22062
Discount Schedule	CP4C
Gtin	00785901142621
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.