

Product data sheet

Specifications



REACTOR DRIVE LINE 3PH

RL00403

⚠ End-of-service on: Nov 24, 2021

⚠ Discontinued

Complementary

Line Rated Current	4 A
Awg Gauge	AWG 22...AWG 14
Depth	4.1 in (104.14 mm)
Electrical Connection	Screw clamp terminal
Height	3.4 in (86.36 mm)
Permissible Voltage	600 V AC
Net Weight	5 lb(US) (2.27 kg)
Protection Type	Current protection Overvoltage protection Harmonic distortion
Width	4.4 in (111.76 mm)

Environment

Nema Degree Of Protection	No enclosure rating (open device)
Product Certifications	UL listed file E180243 CSA LR29753 CE

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
Gtin	00785901514374
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.