

Product data sheet

Specifications



REACTOR DRIVE LINE 3PH 1.5-2HP 208/230V T-1

RL00812

Discontinued on: Jun 15, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Discontinued

Complementary

Line Rated Current	8 A
Awg Gauge	AWG 22...AWG 14
Depth	6 in (152.40 mm)
Electrical Connection	Screw clamp terminal
Height	8 in (203.20 mm)
Permissible Voltage	600 V AC
Net Weight	15 lb(US) (6.80 kg)
Protection Type	Harmonic distortion Overvoltage protection Current protection
Width	8 in (203.20 mm)

Environment

Product Certifications	UL listed file E180243 CE CSA LR29753
------------------------	---

Ordering and shipping details

Category	US1CP4C22062
Discount Schedule	CP4C
Gtin	785901142652
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.99 in (20.3 cm)
Package 1 Width	7.99 in (20.3 cm)
Package 1 Length	5.98 in (15.2 cm)
Package 1 Weight	13.00 lb(US) (5.897 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months