

Product data sheet

Specifications



REACTOR DRIVE LINE 3PH 7.5HP 208/230V OPEN

RL02502

 **End-of-service on:** Nov 24, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

 **Discontinued**

Complementary

Line Rated Current	25 A
Awg Gauge	AWG 22...AWG 5
Depth	5.8 in (147.32 mm)
Electrical Connection	Screw clamp terminal
Height	3.5 in (88.90 mm)
Permissible Voltage	600 V AC
Net Weight	14 lb(US) (6.35 kg)
Protection Type	Harmonic distortion Current protection Overvoltage protection
Width	7.2 in (182.88 mm)

Environment

Nema Degree Of Protection	No enclosure rating (open device)
Product Certifications	CE UL listed file E180243 CSA LR29753

Ordering and shipping details

Category	US1CP4C22062
Discount Schedule	CP4C
Gtin	00785901514480
Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications