# **Product data sheet**

Specification





## socket, Harmony Electromechanical Relays, for RXM2 RXM4 relays, screw connec to rs, mixed contact

RXZE2M114M

Product availability: Stock - Normally stocked in distribution facility

Price\*: 6.10 USD

### Main

Range Of Product	Harmony Electromechanical Relays Harmony Timer Relays
Device Short Name	RXZ
Product Or Component Type	Socket
Product Compatibility	Plug-in relay RXM 2 C/O Plug-in relay RXM 4 C/O
Contacts Type And Composition	4 C/O
[Ith] Conventional Free Air Thermal Current	10 A

### Complementary

Shape Of Pin	Flat
[Ue] Rated Operational Voltage	< 250 V
Contact Terminal Arrangement	Mixed
Connections - Terminals	Connector, 1 x 0.251 x 2.5 mm² AWG 22AWG 14) flexible with cable end Connector, 2 x 0.252 x 1 mm² AWG 22AWG 17) flexible with cable end Connector, 1 x 0.51 x 2.5 mm² AWG 20AWG 14) solid without cable end Connector, 2 x 0.52 x 1.5 mm² AWG 20AWG 16) solid without cable end
Tightening Torque	< 1 N.m M3
Fixing Mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)
[Uimp] Rated Impulse Withstand Voltage	4 kV
Overvoltage Category	III
Pollution Degree	3
Sale Per Indivisible Quantity	10
Width	1.06 in (27 mm)
Net Weight	0.12 lb(US) (0.056 kg)

#### **Environment**

Ip Degree Of Protection	IP20 conforming to IEC 60529
Dielectric Strength	3000 V
Standards	IEC 61984

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	UL CSA Lloyd's
Marking	CE
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Ambient Air Temperature For Operation	-40131 °F (-4055 °C)

# Ordering and shipping details

Category	US10CP221128
Discount Schedule	0CP2
Gtin	3389119404259
Returnability	Yes
Country Of Origin	FR

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.06 in (2.686 cm)
Package 1 Width	1.67 in (4.245 cm)
Package 1 Length	3.12 in (7.918 cm)
Package 1 Weight	0.12 lb(US) (0.054 kg)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.95 in (7.5 cm)
Package 2 Width	3.46 in (8.8 cm)
Package 2 Length	5.51 in (14.0 cm)
Package 2 Weight	1.24 lb(US) (0.561 kg)
Unit Type Of Package 3	S02
Number Of Units In Package 3	120
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	11.81 in (30.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	16.05 lb(US) (7.281 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance




#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### **Dimensions Drawings**

#### **Dimensions**



- (1) Relays(2) Protection module
- (3) Maintaining clamp
- (4) 2 elongated holes Ø 3.5 mm x 6.5 mm / Ø 0.13 in. x 0.25 in.

Connections and Schema

### Wiring Diagram

