

Product availability : Stock - Normally stocked in distribution facility



Price** : 257.92 USD



Main

Product	Surge protection device
Range	Square D

Complementary

Surge Current	40 kA per phase
Voltage Rating	600Y/347 V AC
Number of Phases	3 phases
Wiring Configuration	4-wire
MCOV	510 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED green normal operation
Height	76.20 mm (3 in)
Width	91.44 mm (3.6 in)
Depth	86.36 mm (3.4 in)

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	black plastic
Standards	UL 1449:ed. 4 type I NEC 285 type I CSA C22.2 No 8
Ambient Operating	149 °F (65 °C)

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B

GTIN	00785901210887
Package weight(Lbs)	0.35 kg (0.78 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

