

Product data sheet

Characteristics

SDSA3650D

Surge Protect - 40kA - 600VAC delta - 3P3W - T4X

Product availability : Stock - Normally stocked in distribution facility



Price* : 257.92 USD



Main

Product	Surge protection device
Range	Square D

Complementary

Surge Current	40 kA per phase
Phase	3 phases
Wiring Configuration	3-wire
MCOV	1020 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED, green = normal operation
Height	3 in
Width	3.6 in
Depth	3.4 in

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	Plastic, colour : black
Standards	CSA C22.2 No 8 UL 1449 type I ed. 4 NEC 285 type I
Ambient Operating	149 °F (65 °C)

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B

GTIN	00785901927563
Nbr. of units in pkg.	1
Package weight(Lbs)	1.7
Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1640 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP which is known to the State of California to cause cancer and
----- Substance 2	DIDP which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------