

Product data sheet

Characteristics

SDSA3650E

Surge Protect - 40kA - 600VAC delta - 3P3W - T1

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 257.92 USD



Main

Product	Surge protection device
---------	-------------------------

Complementary

Surge Current	40 kA
Voltage Rating	600 V delta AC
Number of Phases	3 phases
Wiring Configuration	3-wire
Connection	Wire
MCOV	510 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED

Environment

Enclosure Rating	NEMA 1
Enclosure Material	black plastic
Standards	CSA C22.2 No 8 UL 1449:ed. 4

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B
Package weight(Lbs)	0.86 kg (1.9 lb(US))
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP and DIDP which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Approximate Dimensions

