

Product data sheet

Characteristics

SDSA4040D

Surge Protect - 40kA - 480VAC delta - 3P3W - T4X

Product availability : Stock - Normally stocked in distribution facility



Price** : 257.92 USD



Main

Product	Surge protection device
---------	-------------------------

Complementary

Surge Current	40 kA
Voltage Rating	480 V delta AC
Number of Phases	3 phases
Wiring Configuration	3-wire
Connection	Wire AWG 12 copper
MCOV	180 V
Nominal Discharge Current	10 kA
SCCR	200 kA
Local Signalling	Status LED normal operation
Mounting Support	Panel mounting
Height	3.07 in (78 mm)
Width	3.62 in (92 mm)
Depth	2.64 in (67 mm)

Environment

Enclosure Rating	NEMA 4X
Enclosure Material	black plastic
Standards	UL 1449:ed. 4 CSA C22.2 No 8:1986
Ambient Operating	149 °F (65 °C)

Ordering and shipping details

Category	08462 - SURGE PROTECTION SDSA
Discount Schedule	DE1B
GTIN	00785901599920
Package weight(Lbs)	0.43 kg (0.94 lb(US))
Returnability	Yes
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: DINP and DIDP which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.

Approximate Dimensions

