# Product data sheet

Specifications





plug in relay, Harmony Solid State Slim Relays, 2A, random switching, input 3 to 12V DC, output 24 to 280V AC

SSL1A12JDR

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 22.95 USD

#### Main

Range Of Product	Harmony Solid State Relays
Product Or Component Type	Solid state relay up to 10 A
Device Short Name	SSL
Phase	1 phase
Output Switching Mode	Random voltage switching

### Complementary

Mounting Support	Socket
Line Rated Current	2 A
Output Voltage	24280 V AC
[Uc] Control Circuit Voltage	312 V DC
Capacitance Unbalance	1.5 pF input/output
Minimum Switching Voltage	3 V DC turn-on
Maximum Switching Voltage	1 V DC turn-off
Input Current Limits	15 mA
Input Impedance	333 kOhm
Solid State Output Type	Random voltage switching SCR output
Load Current	0.072 A
Tansient Overvoltage	600 V AC
Surge Current	120 A 16.6 ms 115 A 20 ms
Maximum Voltage Drop	<1.1 V on-state
Maximum I <sup>2</sup> T For Fusing	66 A <sup>2</sup> .s for 10 ms at 50 Hz 60 A <sup>2</sup> .s for 8.3 ms at 60 Hz
Maximum Leakage Current	4 mA off-state
Dv/Dt	500 V/µs off-state at maximum voltage
Response Time	0.5 cycle (turn-off) 0.1 ms (turn-on)
Overvoltage Category	Ш
Width	0.20 in (5 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Height	1.10 in (28 mm)
Depth	0.59 in (15 mm)
Net Weight	0.01 lb(US) (0.0041 kg)

## **Environment**

Flame Retardance	V0 conforming to UL 94
Dielectric Strength	2500 V for input/output
Pollution Degree	2
Product Certifications	CSA UL
Marking	CE
Ambient Air Temperature For Operation	-4176 °F (-2080 °C)
Ambient Air Temperature For Storage	-4185 °F (-2085 °C)

# Ordering and shipping details

Category	US10CP222375
Discount Schedule	0CP2
Gtin	3606480579714
Returnability	No
Country Of Origin	MX

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.28 in (0.7 cm)
Package 1 Width	0.98 in (2.5 cm)
Package 1 Length	14.57 in (37 cm)
Package 1 Weight	0.18 oz (5 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	0.28 in (0.7 cm)
Package 2 Width	0.98 in (2.5 cm)
Package 2 Length	14.57 in (37 cm)
Package 2 Weight	2.12 oz (60 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	1080
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	12.53 lb(US) (5.684 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

### **Dimensions Drawings**

#### **Dimensions**




# **Product data sheet**

## SSL1A12JDR

#### Performance Curves

### **Derating Curves**



A : Load Current (Amperes)
B : Ambient Temperature (°C)