

Product data sheet

Characteristics

SSP030SLACSE39

SPD, Type SLACSE, 15 A, 120 V, 39 kA, surface mount, hybrid

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Surge protection device
---------	-------------------------

Complementary

Surge Current	39 kA 10 kA signal
System Voltage	30 V DC
Service Voltage	120 V
Line Rated Current	15 A
Device Mounting	Surface
Height	0.7 in (17.78 mm)
Width	0.7 in (17.78 mm)
Depth	0.3 in (7.62 mm)

Ordering and shipping details

Category	08466 - SURGE PROTECTION HWA
Discount Schedule	DE1B
GTIN	00785901293545
Nbr. of units in pkg.	1
Package weight(Lbs)	63.5
Returnability	Y