

Product availability : Stock - Normally stocked in distribution facility



Main

Product	Surge protection device
Range	SurgeLogic
Device Short Name	EMA

Complementary

Surge Current	160 kA
System Voltage	480Y/277 V AC
Phase	3 phases
Wiring Configuration	4-wire
Connection	Lugs AWG 10...AWG 2 copper Torque to: 4 N.m
MCOV	320 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Local Signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase
Provided Equipment	Surge counter Alarm enable/disable switch Dry contacts
Device Mounting	Surface
Height	11.1 in (282 mm)
Width	9.98 in (253.5 mm)
Depth	5.31 in (135 mm)

Environment

Enclosure Rating	NEMA 1
Enclosure Material	Painted sheet steel, colour : grey
Standards	UL 1283 ed. 5 UL 1449 ed. 4

Ambient Operating	149 °F (65 °C)
-------------------	----------------

Ordering and shipping details

Category	08464 - SURGE PROTECTION EMA
Discount Schedule	DE1B
GTIN	00785901988984
Nbr. of units in pkg.	1
Package weight(Lbs)	15.960000000000001
Returnability	Y
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov