





All in one, Homeline, CSED, ringed socket, 400A, surface/semi, 30 spaces, 40 circuits, 25kA SCCR, 320 manual bypass

SU3040D400CB

Product availability: Stock - Normally stocked in distribution facility

Price\*: 7,167.00 USD

### Main

Product Or Component Type	All-In-One
Range Of Product	Homeline
Meter Socket Type	Ringed
Hub Type	A-L

## Complementary

Line Rated Current	400 A
Short-Circuit Current	25 kA
Mounting	Surface Semi flush with field installed flange kit
Number Of Spaces	30
Number Of Circuits	40
Number Of Tandem Breakers	10
Electrical Connection	Lugs, service ground Studs, line side
Wire Size	AWG 4250 kcmil (aluminium) service ground AWG 4250 kcmil (copper) service ground
Tightening Torque	Terminal screw 250 lb.in, AWG 4250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 4/.0, aluminium/copper Service ground 45 lb.in, AWG 6AWG 1, aluminium/copper Service ground 40 lb.in, AWG 8, aluminium/copper Branch lugs 50 lb.in, AWG 3AWG 2/0, aluminium/copper Branch lugs 35 lb.in, AWG 6AWG 4, aluminium/copper Branch lugs 25 lb.in, AWG 8, aluminium/copper Branch lugs 20 lb.in, AWG 14AWG 10, aluminium/copper Branch lugs 20 lb.in, AWG 12AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service Feed Location	UG
Bypass Type	Class 320 manual bypass
Width	28.25 in (717.55 mm)
Depth	7.50 in (190.50 mm)
Height	41.25 in (1047.75 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Bus Rating 200.0 A

### **Environment**

Nema Rating	NEMA 3R	
Product Certifications	UL Listed	

## Ordering and shipping details

Category	US1DE3A00148
Discount Schedule	DE3A
Gtin	785901521792
Returnability	Yes
Country Of Origin	MX

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.00 in (25.4 cm)
Package 1 Width	29.02 in (73.7 cm)
Package 1 Length	42.01 in (106.7 cm)
Package 1 Weight	112.00 lb(US) (50.802 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information


Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


#### **Dimensions Drawings**

#### **Approximate Dimensions**



#### Connections and Schema

#### **Connections and Wiring Diagrams**



- ONE SINGLE POLE, ONE PLUG-ON SPACE TYPE HOM ONLY. TWO POLE TYPE HOM OR HOMA (125A MAX.) MAY PLUG-ON TWO ADJACENT SPACES. TWO POLE TYPE HOMA (150-200A MAX.) MAY PLUG-ON FOUR ADJACENT SPACES (RIGHT SIDE ONLY).
- TWO SINGLE POLE, ONE PLUG-ON SPACE TYPE HOMT OR ONE SINGLE POLE TYPE HOM. TWO POLE TYPE HOM OR HOMA (125A MAX.) MAY PLUG-ON TWO ADJACENT SPACES. TWO POLE TYPE HOMA (150-200A MAX.) MAY PLUG-ON FOUR ADJACENT SPACES (RIGHT SIDE ONLY).