Product data sheet

Specifications





NEMA Contactor, TeSys N, reversing, Size 1, 27A, 10HP at 460VAC, 3 pole, 3 phase, 208VAC 50/60Hz coil, open

T02CN23LE7

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,183.50 USD

Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Reversing
Nema Size	1
Motor Horsepower Rating Hp	7.5 hp 200 V AC 7.5 hp 230 V AC 10 hp 460 V AC 10 hp 575 V AC

Complementary

Rated Current	27 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	Common control circuit
Number Of Poles	208 V AC
Control Circuit	3P
Coil Volltage	3 phase
Auxiliary Contact Composition	1 NO + 1 NC
Electrical Connection	Screw clamp terminals

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category	US10CP121196	
Discount Schedule	0CP1	
Gtin	3606480573316	
Returnability	Yes	
Country Of Origin	FR	

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.53 in (11.5 cm)
Package 1 Width	4.53 in (11.5 cm)
Package 1 Length	5.71 in (14.5 cm)
Package 1 Weight	2.09 lb(US) (0.949 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov