

Product data sheet

Specifications

SQUARE D



NEMA Contactor, TeSys N, nonreversing, Size 3, 90A, 50HP at 460VAC, 3 pole, 3 phase, 240VAC 60Hz coil, open

T02EN13U6

⚠ Discontinued

Main

Product Type	Contactor
Range	TeSys N
Contactor Type	Non-reversing
Nema Size	3
Motor Horsepower Rating Hp	25 hp 200 V AC 30 hp 230 V AC 50 hp 460 V AC 50 hp 575 V AC

Complementary

Rated Current	90 A
[Ue] Rated Operational Voltage	600 V AC
Network Phases	3 phase
Number Of Poles	3P
Control Circuit	Common control circuit
Coil Volltage	240 V AC
Auxiliary Contact Composition	1 NO
Electrical Connection	Lugs ordered separately
Height	6.38 in (162.05 mm)
Width	6.44 in (163.58 mm)
Depth	6.68 in (169.67 mm)
Product Weight	9.06 lb(US) (4.11 kg)

Environmental

Product Certifications	UL Listed CSA
Nema Degree Of Protection	Not rated (open device)

Ordering and shipping details

Category	21197-TESYS N CONTACTORS SIZES 3 - 7
Discount Schedule	CP1
Returnability	No
Country Of Origin	CZ

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

