

Product data sheet

Specifications



Motor Starter, TeSys NEMA,
nonreversing, Size 00, 9A, 3 pole,
HP rated, Motor Logic SSOLR, 120
VAC 60 Hz coil, open

T36AN13G7

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 323.00 USD

Main

Product	Starter
Range Of Product	TeSys N
Current Rating	9 A
Certifications	UL Listed CSA
Control Circuit Type	Common control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO + 1 NC
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	00
Control Circuit Voltage	120 V AC
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Overload Type	Solid state Motor Logic class 10/20 3...9 A

Ordering and shipping details

Category	US10CP121198
Discount Schedule	0CP1
Gtin	785901955269
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	10.50 in (26.67 cm)
Package 1 Width	10.50 in (26.67 cm)
Package 1 Length	8.00 in (20.32 cm)
Package 1 Weight	5.92 lb(US) (2.685 kg)

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov