


# Product data sheet

Specifications

SQUARE D



## TeSys NEMA Sz 0 rev open starter, 3P, 24 VAC, Sprt Ctrl

T36BN23B7S

Discontinued on: Jun 30, 2020

Discontinued

### Main

Product	Starter
Range Of Product	TeSys N
Current Rating	18 A
Certifications	UL Listed CSA
Control Circuit Type	Separate control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO + 1 NC
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	0
Control Circuit Voltage	24 V AC
Starter Type	Reversing
Electrical Connection	Screw clamp terminals
Overload Type	Solid state Motor Logic class 10/20 6...18 A

### Ordering and shipping details

Category	21198-TESYS N STARTERS SIZES 00 - 2
Discount Schedule	CP1
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - <a href="#">www.P65Warnings.ca.gov</a>	