


Product data sheet

Specifications

SQUARE D



TeSys NEMA Sz 1 rev open starter, 3P, 24 VAC

T36CN23B7

⚠ Discontinued on: Jun 30, 2020

⚠ Discontinued

Main

Product	Starter
Range Of Product	TeSys N
Current Rating	27 A
Certifications	UL Listed CSA
Control Circuit Type	Common control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO + 1 NC
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	1
Control Circuit Voltage	24 V AC
Starter Type	Reversing
Electrical Connection	Screw clamp terminals
Overload Type	Solid state Motor Logic class 10/20 9...27 A

Ordering and shipping details

Category	21198-TESYS N STARTERS SIZES 00 - 2
Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability




Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Reach Free Of Svhc	
 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov