

Product data sheet

Specifications



TeSys NEMA Sz 4 open starter, 3P, 480 VAC

T36FN13Q5

! Discontinued

Main

Product	Starter
Range Of Product	TeSys N
Current Rating	135 A
Certifications	UL Listed CSA
Control Circuit Type	Common control circuit
Enclosure Type	Not rated (open device)
Auxiliary Contacts	1 NO
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Number Of Poles	3P
Phase	3 phase
Maximum Voltage Rating	600 V AC
Nema Size	4
Control Circuit Voltage	480 V AC
Starter Type	Non reversing
Electrical Connection	Lugs ordered separately
Overload Type	Solid state Motor Logic class 10/20 45...135 A

Ordering and shipping details

Category	21199-TESYS N STARTERS SIZES 3 - 7
Discount Schedule	CP1
Returnability	No
Country Of Origin	CZ

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.30 lb(US) (7.394 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
