

Price** : 3,828.00 USD



T40AA128BD4JAP1 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Self-protected combination motor controller
Range of product	TeSys N Self-Protected Combination Motor Controller
Product certifications	CSA UL listed
Control circuit	Factory wired power supply
Provided equipment	Power supply
Phase	3 phases
[Ue] rated operational voltage	480Y/277 V AC
[Uc] control circuit voltage	24 V DC
Communication port protocol	AS-Interface
NEMA degree of protection	NEMA 12/3R
Enclosure material	Painted sheet steel
Enclosure type	Standard size
Enclosure accessory description	With external reset
Auxiliary contact composition	1 NO + 1 NC
NEMA size	00
Maximum Horse Power Rating	2 hp 460 V AC
Poles description	3P
Local signalling	Red indicator on LED
Control type	Push-button START-STOP)
Motor starter type	Non reversing
Electrical connection	Screw-clamp terminals
Thermal overload type	Solid state advanced class 20 3...12 A
Disconnecter device type	Self-protected combination controller 9 A

Ordering and shipping details

Category	21219-ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Package weight(Lbs)	24.62 lb(US) (11.167 kg)
Returnability	No

Contractual warranty

Warranty	18 months
----------	-----------
