

Product data sheet

Specifications



SZ00 FVNR COMBO 12/3R SC FLA 5

T40AA129G7NC12S

! Discontinued

Main

Product Or Component Type	Self-protected combination motor controller
Range Of Product	TeSys N Self-Protected Combination Motor Controller
Product Certifications	UL Listed CSA
Control Circuit	Separate control circuit
Phase	3 phase
[Ue] Rated Operational Voltage	208Y/120 V AC
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz
Communication Port Protocol	Without
Nema Degree Of Protection	NEMA 12/3R
Enclosure Material	Painted sheet steel
Enclosure Type	Standard size
Enclosure Accessory Description	With external reset
Auxiliary Contact Composition	1 NO + 1 NC
Nema Size	00
Maximum Horse Power Rating	2 hp 460 V AC 1.5 hp 230 V AC 1.5 hp 200 V AC
Poles Description	3P
Local Signalling	Red/green indicator on/off LED
Control Type	Selector switch HAND-OFF-AUTO)
Motor Starter Type	Non reversing
Electrical Connection	Screw-clamp terminals
Thermal Overload Type	Solid state advanced class 20 1.25...5 A
Disconnecter Device Type	Self-protected combination controller 9 A

Ordering and shipping details

Category	21219-ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	24.62 lb(US) (11.167 kg)

Contractual warranty

Warranty	18 months
----------	-----------