


Price* : 2858.00 USD



T40AG125BDJCP1S6 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Self-protected combination motor controller
Range of product	TeSys N Self-Protected Combination Motor Controller
Product certifications	CSA UL listed
Control circuit	Separate control circuit
Provided equipment	Current limiter
Phase	3 phases
System Voltage	600 V AC
[Uc] control circuit voltage	24 V DC
Communication port protocol	AS-Interface
NEMA degree of protection	NEMA 1
Enclosure material	Painted sheet steel
Enclosure type	Standard size
Enclosure accessory description	With external reset
Auxiliary contact composition	1 NO + 1 NC
NEMA size	00
Motor power hp	2 hp 460 V AC 2 hp 575 V AC 1.5 hp 200 V AC 1.5 hp 230 V AC
Poles description	3P
Local signalling	Red indicator on LED
Control type	Selector switch HAND-OFF-AUTO
Motor starter type	Non reversing
Electrical connection	Screw-clamp terminals
Thermal overload type	Solid state advanced class 20 0.15...0.6 A
Disconnecter device type	Self-protected combination controller 9 A

Ordering and shipping details

Category	21219 - ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	24.62000000000001

Returnability	N
---------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
