

Product data sheet

Specifications



SZ00 FVNR COMBO 1 SC FLA 12

T40AG128G7NAP1S6

! Discontinued

Main

Product Or Component Type	Self-protected combination motor controller
Range Of Product	TeSys N Self-Protected Combination Motor Controller
Product Certifications	UL Listed CSA
Control Circuit	Separate control circuit
Provided Equipment	Current limiter
Phase	3 phase
[Ue] Rated Operational Voltage	600 V AC
[Uc] Control Circuit Voltage	120 V AC 50/60 Hz
Communication Port Protocol	Without
Nema Degree Of Protection	NEMA 1
Enclosure Material	Painted sheet steel
Enclosure Type	Standard size
Enclosure Accessory Description	With external reset
Auxiliary Contact Composition	1 NO + 1 NC
Nema Size	00
Maximum Horse Power Rating	2 hp 460 V AC 1.5 hp 230 V AC 1.5 hp 200 V AC 2 hp 575 V AC
Poles Description	3P
Local Signalling	Red indicator on LED
Control Type	Push-button START-STOP)
Motor Starter Type	Non reversing
Electrical Connection	Screw-clamp terminals
Thermal Overload Type	Solid state advanced class 20 3...12 A
Disconnecter Device Type	Self-protected combination controller 9 A

Ordering and shipping details

Category	21219-ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	24.62 lb(US) (11.167 kg)

Contractual warranty

Warranty	18 months
----------	-----------