

# Product data sheet

Specifications



## SZ0 FVNR COMBO 12/3R PS ASI FLA 1.4

T40BA126BD1JCP1

⚠ Discontinued

### Main

|                                 |                                                     |
|---------------------------------|-----------------------------------------------------|
| Product Or Component Type       | Self-protected combination motor controller         |
| Range Of Product                | TeSys N Self-Protected Combination Motor Controller |
| Product Certifications          | UL Listed<br>CSA                                    |
| Control Circuit                 | Factory wired power supply                          |
| Provided Equipment              | Power supply                                        |
| Phase                           | 3 phase                                             |
| [Ue] Rated Operational Voltage  | 120/240 V AC                                        |
| [Uc] Control Circuit Voltage    | 24 V DC                                             |
| Communication Port Protocol     | AS-Interface                                        |
| Nema Degree Of Protection       | NEMA 12/3R                                          |
| Enclosure Material              | Painted sheet steel                                 |
| Enclosure Type                  | Standard size                                       |
| Enclosure Accessory Description | With external reset                                 |
| Auxiliary Contact Composition   | 1 NO + 1 NC                                         |
| Nema Size                       | 0                                                   |
| Maximum Horse Power Rating      | 3 hp 230 V AC<br>3 hp 200 V AC                      |
| Poles Description               | 3P                                                  |
| Local Signalling                | Red indicator on LED                                |
| Control Type                    | Selector switch HAND-OFF-AUTO)                      |
| Motor Starter Type              | Non reversing                                       |
| Electrical Connection           | Screw-clamp terminals                               |
| Thermal Overload Type           | Solid state advanced class 20 0.3...1.4 A           |
| Disconnecter Device Type        | Self-protected combination controller 18 A          |

### Ordering and shipping details

|                   |                                        |
|-------------------|----------------------------------------|
| Category          | 21219-ENCLOSED TESYS N COMB STR SIZE 1 |
| Discount Schedule | CP1                                    |
| Returnability     | No                                     |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 24.62 lb(US) (11.167 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|