


Price** : 2,945.00 USD



T40CG1N3V81NCP1 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Self-protected combination motor controller
Range of product	TeSys N Self-Protected Combination Motor Controller
Product certifications	UL listed CSA
Control circuit	Control circuit transformer
Provided equipment	2 fuses (primary), 1 fuse (secondary)
Phase	3 phases
System Voltage	480Y/277 V AC
[Uc] control circuit voltage	120 V AC 50/60 Hz
Communication port protocol	Without
NEMA degree of protection	NEMA 1
Enclosure material	Painted sheet steel
Enclosure type	Standard size
Enclosure accessory description	With external reset
Auxiliary contact composition	1 NO + 1 NC
NEMA size	1
Motor power hp	10 hp 460 V AC
Poles description	3P
Local signalling	Red indicator on LED
Control type	Selector switch HAND-OFF-AUTO
Motor starter type	Non reversing
Electrical connection	Screw-clamp terminals
Thermal overload type	No thermal overload to be ordered separately
Disconnecter device type	Self-protected combination controller 27 A

Ordering and shipping details

Category	21219 - ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	24.620000000000001
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
