

Product data sheet

Characteristics

TCSECE3M3M5S4

Ethernet ConneXium cable - shielded twisted pair
- 2 x rugged RJ45 - CE - 5 m

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 155.00 USD



Main

Range of product	ConneXium
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Product or component type	Shielded twisted pair straight cable
Accessory / separate part destination	Ethernet network
Cable length	16.4 ft (5 m)

Complementary

Transmission support medium	Twisted shielded pairs cable
Communication network category	5e
AWG gauge	AWG 24
Electrical connection	2 connectors RJ45 8 straight
Marking	CE
Cover material	PUR

Environment

IP degree of protection	IP20
Standards	EIA/TIA-568 category CAT 5E EN 50173 class D IEC 11801 class D
Environmental characteristic	Halogen free Low smoke emission
Flame retardance	Class C2 conforming to CEI 322/1 Class C2 conforming to NF C 32070-1

Ordering and shipping details

Category	18225 - PLC NTRWK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	003595864142975
Nbr. of units in pkg.	1

Package weight(Lbs)	0.5799999999999996
Returnability	N
Country of origin	TH

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------