

Product data sheet

Characteristics

TCSWABP68

overvoltage protector for antenna - frequency range 2 to 6 GHz

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 225.00 USD



Main

Accessory / separate part category	Protection accessories
Accessory / separate part type	Protector
Product or component type	Overvoltage protector for antenna
Range compatibility	ConneXium
Attenuation	<= 0.2 dB 2...6 kHz

Complementary

Cable length	1.64 ft (0.5 m)
Outer dimension	90 x 27 x 12 mm
Product weight	0.06 lb(US) (0.025 kg)

Environment

Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Relative humidity	0...95 % without condensation
IP degree of protection	IP67
Product certifications	CUL 1604 Class 1 Division 2 Germanischer Lloyd (GL) CUL 508

Ordering and shipping details

Category	18225 - PLC NTRK HRDWR & PROWORX SOFTWARE
Discount Schedule	PC41
GTIN	003595864106052
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	N
Country of origin	CH

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
	Will not be compliant

Contractual warranty

Warranty period	18 months
-----------------	-----------
