

TM171AETHRS485

Modicon M171 Performance Plug-in Ethernet and BACnet MSTP or Modbus

Product availability : Stock - Normally stocked in distribution facility

Price* : 91.46 USD



Main

Range of product	Modicon M171
Product or component type	Communication module
Communication port protocol	Ethernet HTTP Modbus RTU Modbus TCP SMTP BACnet MS/TP BACnet IP RS485

Complementary

Integrated connection type	Ethernet RJ45 - twisted pair RS485 wire crimp - twisted pair
Adjustment	Pitch 3.81 mm
Electrical connection	Removable screw terminal block
Physical interface	90° insertion - 0 in ² (2.5 mm ²) cable RJ45
Supply	Via base board EVD/EVC
Product compatibility	Logic controller M171 performance
Product weight	0.17 lb(US) (0.077 kg)

Environment

Product certifications	CE CSA cURus EAC
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Ambient air temperature for storage	-4...185 °F (-20...85 °C)
Relative humidity	10...90 % without condensation

Ordering and shipping details

Category	22537 - M171 / M172 HVAC CONTROLLERS
Discount Schedule	PC12
GTIN	00785901503286
Nbr. of units in pkg.	1
Package weight(Lbs)	0.41000000000000003
Returnability	Y
Country of origin	IT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1429 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov