

Product data sheet

Characteristics

TM171DGRP

Modicon M171 Performance Display Graphic

Product availability : Stock - Normally stocked in distribution facility

Price* : 219.65 USD



Main

Range of product	Modicon M171
Product or component type	Display module
Display colour	Monochrome
Supply	External source

Complementary

Display type	Matrix backlit LCD
Number of key	5
Display resolution	240 x 140 pixels
Color	Grey
[Us] rated supply voltage	12 V AC 24 V DC 24 V AC
Power consumption in W	5 W 0 W
Marking	CE
Realtime clock	With realtime clock
Local signalling	1 LED red 1 LED yellow 1 LED green
Product compatibility	Logic controller M171 performance
Height	6.3 in (160 mm)
Width	3.54 in (90 mm)
Depth	1.06 in (27 mm)
Product weight	0.43 lb(US) (0.197 kg)

Environment

Standards	RoHS compliant
Product certifications	cURus REACH
IP degree of protection	IP65 on front face

Ordering and shipping details

Category	22537 - M171 / M172 HVAC CONTROLLERS
Discount Schedule	PC12
GTIN	00785901595809
Nbr. of units in pkg.	1
Package weight(Lbs)	0.70999999999999996
Returnability	Y
Country of origin	IT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1427 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov