

Product data sheet

Characteristics

TRAI3500SC07

Square D, ReactiVar™, split core current transformer, 25VA, 3500:5 A, 7x4"

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,019.00 USD



Main

Range	Square D
Product or component type	Current transformer
Accessory / separate part category	Measurement accessory

Complementary

Range compatibility	Square D ReactiVar capacitor bank
Current transformer type	Split core
Primary operational current	3500 A
Secondary current	5 A
Network type	AC
Network frequency	60 Hz
Current transformer ratio	3500/5
Burden	25 VA
Mounting location	Indoor use only
Width	Internal: 177.8 mm
Height	Internal: 101.6 mm

Ordering and shipping details

Category	00050 - PWR FACT. CAP - AUTOMATIC
Discount Schedule	DE2C
Nbr. of units in pkg.	1
Package weight(Lbs)	5
Returnability	N

Contractual warranty

Warranty period	18 months
-----------------	-----------
