## Product data sheet

Specification





# Ethernet switchboard display FDM 121, 1 connected device, screen 96mm x 96mm, IP54 on front face

TRV00121

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,500.00 USD

### Main

Device Short Name	FDM121
Product Or Component Type	Display module
Accessory / Separate Part Category	Display and signalling accessory
Range Compatibility	MasterPact MTZ
	MasterPact NW
	MasterPact NT
	Compact NSX
	ComPact ComPact NS630b1600
	ComPact ComPact NS1600b3200
	PowerPact PowerPact H
	PowerPact PowerPact J
	PowerPact PowerPact L
	PowerPact PowerPact P
	PowerPact PowerPact R
Product Name	Enerlin'X FDM
Function Of Module	Remote control
	View network
	Metering
	Display alarm
	• •

### Complementary

Control Type	Remote control	
Mounting Mode	Flush mounting	
Mounting Support	Surface mount with kit Door cut-out	
Display Type	LCD screen with white backlighting	
Display Resolution	128 x 128 pixels	
View Angle Horizontal X Vertical	60 x 30°	
[Us] Rated Supply Voltage	24 V DC - 2010 %	
Current Consumption	21 mA	
Standards	CE CSA UL	
Height	3.78 in (96 mm)	
Width	3.78 in (96 mm)	
Depth	1.32 in (33.6 mm)	
Accessory / Separate Part Category	Spare part ComPact NS630b1600 Spare part ComPact NS1600b3200	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Ip Degree Of Protection	IP53 front face:
Ambient Air Temperature For Operation	14131 °F (-1055 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)

## Ordering and shipping details

Category	US10DE201103
Discount Schedule	0DE2
Gtin	3606480025389
Returnability	No
Country Of Origin	CN

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.28 in (5.803 cm)
Package 1 Width	4.05 in (10.275 cm)
Package 1 Length	4.08 in (10.375 cm)
Package 1 Weight	8.62 oz (244.5 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	34
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	316.30 oz (8967 g)
Unit Type Of Package 3	P12
Number Of Units In Package 3	816
Package 3 Height	37.40 in (95 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	7908.57 oz (224208 g)

## **Contractual warranty**



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov