

Product data sheet

Characteristics

TSXCANCADD5

CANopen cordset - molded female SUB-D9 connectors - standard - IP20 - 5 m

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 104.00 USD



Main

Range of product	CANopen
Bus type	CANopen
Accessory / separate part category	Connection accessories
Accessory / separate part type	Connecting cable
Accessory / separate part destination	CANopen bus
Cable length	16.4 ft (5 m)

Complementary

Electrical connection	2 female connectors SUB-D 9 pin(s)
Marking	CE
Product weight	0.97 lb(US) (0.44 kg)

Environment

IP degree of protection	IP20
-------------------------	------

Ordering and shipping details

Category	22531 - PLCS, TWIDO, TWD
Discount Schedule	PC12
GTIN	003595863860184
Nbr. of units in pkg.	1
Package weight(Lbs)	0.9699999999999997
Returnability	N
Country of origin	PT

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1005 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------
