

TSXCDP302

rolled ribbon connecting cable - for I/O module
with HE10 connectors - 3 m

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 114.00 USD



Main

Range of product	Modicon Premium Automation platform
Accessory / separate part designation	Rolled ribbon connecting cable
Accessory / separate part type	Connecting cable
Accessory / separate part category	Connection accessories
Accessory / separate part destination	I/O module fitted with HE10 connectors Telefast 2 sub-base
Product specific application	Auxiliary inputs supply 24 V DC Encoder supply 5 V/10...30 V DC

Complementary

Product compatibility	ABE7H08R10 ABE7H16R20 TSXCTY2C
Cable length	9.84 ft (3 m)
Electrical connection	2 connectors HE10 20 ways
Wire section	0 in ² (0.08 mm ²)
AWG gauge	AWG 28
Current per channel	<= 0.1 A
Product weight	0.55 lb(US) (0.25 kg)

Ordering and shipping details

Category	22556 - TSX MICRO, PL7 MICRO & ACCESS
Discount Schedule	PC14
GTIN	00785901603092
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N

Country of origin	CN
-------------------	----

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1001 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------