

TSXETY110WSC

Ethernet TCP/IP module - 10 Mbit/s - web server class C10 - Humiseal 1A33

Product availability : Non-Stock - Not normally stocked in distribution facility

Price* : 5,701.70 USD



⚠ Discontinued

TSXETY110WSC has not been replaced. Please contact your customer care center for more information.

Main

Range of product	Modicon Premium Automation platform
Product or component type	Ethernet TCP/IP module
Physical interface	AUI 100BASE-5 1 AUI cable RJ45 10BASE-T 1 twisted pair
Transmission rate	10 Mbit/s
Communication service	Modbus TCP messaging Optional TCP open SNMP agent Uni-TE messaging Common words Ethway/X-Way Application to application Ethway/X-Way
Supply	Via the power supply of the rack
Local signalling	1 LED collision detection (COL) 1 LED Ethernet network status (RUN) 1 LED Ethernet port fault (ERR) 1 LED transmission/reception activity (TX/TR)

Complementary

Communication port protocol	Modbus TCP Uni-Telway Ethway/X-Way
Maximum number of connections	64
Web server	Transparent ready class C10
Web feature	Data Editor (via PC terminal) FactoryCast configurable Rack viewer
Memory description	User web page size 1.4 MB
Marking	CE
Product compatibility	PL7 Pro
Current consumption	1200 mA 5 V DC with remote power supply (AUI) 800 mA 5 V DC without remote power supply (RJ45)
Module format	Standard
Product weight	0.82 lb(US) (0.37 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	EN 61131-2 FM Class 1 Division 2 group A FM Class 1 Division 2 group B FM Class 1 Division 2 group C FM Class 1 Division 2 group D
Product certifications	CSA 1010-1 UL 508
IP degree of protection	IP20
Protective treatment	Conformal coating Humiseal 1A33
Ambient air temperature for operation	32...140 °F (0...60 °C)
Relative humidity	10...95 % at 140 °F (60 °C) without condensation

Ordering and shipping details

Category	22558 - TSX PREMIUM, ATRIUM & PL7 PRO
Discount Schedule	PC22
GTIN	003595863941616
Nbr. of units in pkg.	1
Package weight(Lbs)	2.21
Returnability	N
Country of origin	FR

Offer Sustainability


RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Standard and Extendable Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) With screw terminal block modules.
- (2) Maximum depth for all types of modules and their associated connectors.