

# Product data sheet

## Characteristics

# TVS9HWA80X

Surge Protect - HWA - 80kA - 600VAC delta - 3P3W - T4X

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 3,393.00 USD



### Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	HWA

### Complementary

Surge Current	80 kA per phase
System Voltage	600 V delta AC
Phase	3 phases
Wiring Configuration	3-wire
Connection	Wire phase and neutral AWG 10 copper Wire ground AWG 10 copper Wire dry contacts AWG 22 copper
MCOV	840 V
Nominal Discharge Current	20 kA
Max Number of Poles	1
SCCR	200 kA
Local Signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase Alarm = fault
Mounting Location	Bottom of enclosure
Device Mounting	Surface Flush with fixing kit
Height	4.8 in (122 mm)
Width	8.62 in (219 mm)
Depth	3.11 in (79 mm)

## Environment

Enclosure Rating	NEMA 4X
Enclosure Material	Plastic, colour : black
Standards	CSA C22.2 No 8 1986 UL 1283 ed. 5 UL 1449 ed. 4
Ambient Operating	149 °F (65 °C)

## Ordering and shipping details

Category	08466 - SURGE PROTECTION HWA
Discount Schedule	DE1B
GTIN	00785901691242
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8999999999999999
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1743 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	DINP which is known to the State of California to cause cancer and
----- Substance 2	DIDP which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------