

Product data sheet

Characteristics

TVS91MA180

Surge Protect - IMA - 240kA - 600VAC delta - 3P3W - T2

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 7,760.00 USD



Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	IMA

Complementary

Surge Current	240 kA per phase
System Voltage	600 V delta AC
Phase	3 phases
Wiring Configuration	3-wire
Connection	Lugs AWG 12...AWG 2 aluminium/copper Torque to: 35.4 lbf.in (4 N.m)
MCOV	700 V
Nominal Discharge Current	20 kA
SCCR	200 kA
Provided Equipment	Alarm enable/disable switch Diagnostic display Backplane Cables
Height	6.13 in (155.7 mm)
Width	9.86 in (250.4 mm)
Depth	3.65 in (92.7 mm)

Environment

Enclosure Rating	NEMA 2
Standards	UL 1283 IEC 61643-1 CSA C22.2 No 8 1986 UL 96A ed. 12 UL 1449 ed. 4

Ordering and shipping details

Category	08252 - TVSS UNIT
Discount Schedule	PE1A
Nbr. of units in pkg.	1
Package weight(Lbs)	8.4000000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------