

Product data sheet

Characteristics

UT3R1121B

HORIZONTAL METER SOCKET RINGLESS OH/ UG 100A 3 POS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 560.00 USD



Main

Product or component type	Meter Socket
Rated Current	100 A
Number of meter sockets	3
Phase	1 phase
System Voltage	600 V AC

Complementary

Number of jaws	4 without jaw release
Bypass type	No bypass
Meter socket type	Ringless
Product certifications	UL listed
Enclosure Rating	NEMA 3R
Box number	13R1
Wire Gauge	AWG 6...250 kcmil (aluminium) main lugs AWG 6...250 kcmil (copper) main lugs AWG 8...AWG 2/0 (aluminium) branch lugs AWG 8...AWG 2/0 (copper) branch lugs
Service feed location	OH UG
Wiring configuration	3-wire
Hub type	A ACP closing plate

Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
GTIN	00785901205159
Nbr. of units in pkg.	1

Package weight(Lbs)	33.160000000000004
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel (Metallic) which is known to the State of California to cause cancer and
----- Substance 2	Toluene which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------