

UT6R1131B

HORIZONTAL METER SOCKET RINGLESS OH/ UG 100A 6 POS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,157.00 USD



Main

Product or component type	Meter Socket
Rated Current	100 A
Number of meter sockets	6
Phase	1 phase
System Voltage	600 V AC

Complementary

Number of jaws	4 without jaw release
Bypass type	No bypass
Meter socket type	Ringless
Product certifications	UL listed
Enclosure Rating	NEMA 3R
Box number	16R
Wire Gauge	AWG 8...AWG 2/0 (aluminium) branch lugs AWG 8...AWG 2/0 (copper) branch lugs AWG 6...350 kcmil (aluminium) main lugs AWG 6...350 kcmil (copper) main lugs
Service feed location	OH UG
Wiring configuration	3-wire
Hub type	A ACP closing plate

Ordering and shipping details

Category	00039 - METER SOCKETS & HUBS
Discount Schedule	DE4
Nbr. of units in pkg.	1
Package weight(Lbs)	67

Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel (Metallic) which is known to the State of California to cause cancer and
----- Substance 2	Toluene which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------