# **Product data sheet**

Specification





### Switch disconnector, TeSys Control, for ON/emergency stop, 20A(V01), 4 screws fixing, for mounting on door

VCF01

Product availability: Stock - Normally stocked in distribution facility

Price\*: 147.00 USD

#### Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Type	Emergency stop switch disconnector

#### Complementary

Device Composition	Handle Switch
Mounting Support	Handle door Switch door
Mounting Method	By 4 screws handle
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Ue] lec Rated Operational Voltage	690 V AC 50/60 Hz
lec Rated Operational Power In W	7.5 kW 500 V AC-3) 11 kW 690 V AC-23A) 3 kW 230240 V AC-3) 4 kW 400415 V AC-3) 7.5 kW 500 V AC-23A) 5.5 kW 690 V AC-3) 4 kW 230240 V AC-23A) 5.5 kW 400415 V AC-23A)
[le] Rated Operational Current	11 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	20 A
[Ithe] Conventional Enclosed Thermal Current	16 A
Making Capacity ( I Rms)	200 A 400 V AC-21A 200 A 400 V AC-22A 200 A 400 V AC-23A
Breaking Capacity	200 A 400 V AC-21A) 200 A 400 V AC-22A) 200 A 400 V AC-23A)
Rated Conditional Short Circuit Current	10 kA 400 V 20 A aM 10 kA 400 V 20 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA 400 V at Ipeak

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

[Icw] Rated Short Time Withstand Current	300 A 400 V 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV
Suitability For Isolation	Yes
Network Type	AC DC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Color	Red
Handle Front Plate Color	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 0.160.31 in (48 mm)
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-15
lec Terminal Connection	Power circuit screw clamp terminals 0.02 in² (10 mm²) solid Power circuit screw clamp terminals 0.01 in² (6 mm²) flexible - with cable end
Tightening Torque	Power circuit 18.59 lbf.in (2.1 N.m) screw clamp terminals
Base Dimension	60 x 60 mm
Height	2.91 in (74 mm)
Width	2.36 in (60 mm)
Product Weight	0.55 lb(US) (0.25 kg)

### **Environment**

Standards	IEC 60947-3
Product Certifications	CCC GL CSA UL UKCA
Degree Of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	тс
Mechanical Robustness	Vibrations 10150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature For Operation	-4122 °F (-2050 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	Main switch disconnector

# Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
Gtin	3389110448924
Returnability	Yes
Country Of Origin	CZ

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.500 cm)
Package 1 Width	3.35 in (8.500 cm)
Package 1 Length	5.12 in (13.000 cm)
Package 1 Weight	7.72 oz (219.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	12.62 lb(US) (5.726 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	121.05 lb(US) (54.908 kg)

### **Contractual warranty**

Apr 25, 2024

Warranty 18 months

### Sustainability Screen Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Toxic Heavy Metal Free
<b>②</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>②</b>	Pvc Free
<b>⊘</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov