# Product data sheet

Specifications





# Enclosed switch disconnector,TeSys Control,for ON/emergency stop,32A,IP65

VCF2GE

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 287.00 USD

#### Main

Range	TeSys	
Product Name	TeSys VARIO	
Device Short Name	VCF	
Product Or Component Type	Enclosed emergency stop switch disconnector	
Performance Level	High performance	
Poles Description	3P	
Control Type	Rotary handle	
Handle Colour	Red	
Handle Front Plate Colour	Yellow	
Rotary Handle Padlocking	1 to 3 padlocks 0.160.31 in (48 mm)	

### Complementary

Marking	0 - 1
[Ue] Rated Operational Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	8 KV
[Ithe] Conventional Enclosed Thermal Current	32 A
[le] Rated Operational Current	29 A AC-23A)400 V
Rated Operational Power In W	15 kW 400 V AC-23) 11 kW 400 V AC-3)
Intermittent Duty Class	30
Making Capacity ( I Rms)	400 A 400 V AC-21A 400 A 400 V AC-22A 400 A 400 V AC-23A
[Icm] Rated Short-Circuit Making Capacity	1 kA 400 V at Ipeak
[Icw] Rated Short-Time Withstand Rms Current	480 A 400 V 1 s
Rated Conditional Short-Circuit Current	10 kA 400 V 50 A aM 10 kA 400 V 50 A gG
Breaking Capacity	320 A 400 V AC-21A) 320 A 400 V AC-22A) 320 A 400 V AC-23A)
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-15

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environmental Characteristic	Standard environment
Suitability For Isolation	Yes
Connections - Terminals	screw clamp terminals 0.02 in² (10 mm²) solid screw clamp terminals 0.01 in² (6 mm²) flexible - with cable end
Tightening Torque	18.59 lbf.in (2.1 N.m) screw clamp terminals
Fire Resistance	1760 °F (960 °C) IEC 60595-2-1
Handle Front Plate Dimension	60 x 60 mm
Height	5.75 in (146 mm)
Width	3.54 in (90 mm)
Depth	5.16 in (131 mm)
Net Weight	1.10 lb(US) (0.5 kg)

### Environment

Standards	IEC 60204 IEC 60947-4-1
Protective Treatment	тс
Ip Degree Of Protection	IP65 conforming to IEC 60529
Mechanical Robustness	Vibrations 10150 Hz 1 gn) IEC 60068-2-6 Shocks 11 ms 30 Gn) IEC 60068-2-27
Ambient Air Temperature For Operation	-4122 °F (-2050 °C)

# Ordering and shipping details

Category	US10CP121730	
Discount Schedule	0CP1	
Gtin	3389110194104	
Returnability	No	
Country Of Origin	CZ	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.45 in (11.3 cm)
Package 1 Width	5.71 in (14.5 cm)
Package 1 Length	6.22 in (15.8 cm)
Package 1 Weight	16.68 oz (473 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.33 lb(US) (3.777 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	56

Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	88.72 lb(US) (40.244 kg)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov