



Main

Product or component type	Additional output module
Range compatibility	Altivar Easy 610 Altivar Process ATV600 Altivar Process ATV900 Altivar Machine ATV340
Input/Output type	3 relay output(s)
Discrete output number	3
Discrete output type	(R4, R5, R6) relay normally open, sampling time: <= 1 ms

Complementary

Electrical durability	100000 cycles
Minimum switching current	5 mA for 24 V DC
Maximum switching current	2 A at 250 V AC on inductive load, cos phi = 0.4 and L/R = 5 ms 2 A at 30 V DC on inductive load, cos phi = 0.4 and L/R = 5 ms 5 A at 250 V AC on resistive load, cos phi = 1 and L/R = 5 ms 5 A at 30 V DC on resistive load, cos phi = 1 and L/R = 5 ms
Electrical connection	Screw terminal block, 1.5 mm ² / AWG 16, 0.5 N.m
Product weight	0.88 lb(US) (0.4 kg)

Ordering and shipping details

Category	22207 - ATV630 FRAMES 5 & 6
Discount Schedule	CP4E
GTIN	00785901969211
Nbr. of units in pkg.	1
Package weight(Lbs)	0.31
Returnability	Y
Country of origin	ID

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1432 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:

----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov
