

Product availability : Stock - Normally stocked in distribution facility

Price* : 335.00 USD



Main

Range of product	Altivar
Product or component type	Analog encoder interface module
Range compatibility	Altivar Process ATV900 Altivar Machine ATV340 Altivar Process Modular
Encoder type	SinCos Hiperface 1 Vpp
[Us] rated supply voltage	5 V DC (voltage limits: 4.75...5.25 V) 12 V DC (voltage limits: 11.4...12.6 V) 24 V DC (voltage limits: 22.8...25.2 V)

Complementary

Supply current	<= 0.25 A (5 V DC) <= 0.1 A (12 V DC) <= 0.05 A (24 V DC)
Protection type	Overload protection Short-circuit protection
Cable distance between devices	<= 100 m
Maximum operating frequency	100 kHz
Input signal	Data+, Data-, Sin, RefSin, Cos, RefCos, Temp+, Temp-
Output signal	Data+, Data-
Connector type	1 female high density SUB-D 15
Product weight	0.33 lb(US) (0.15 kg)

Ordering and shipping details

Category	22209 - ATV650
Discount Schedule	CP4E
GTIN	00785901670124
Nbr. of units in pkg.	1
Package weight(Lbs)	0.3300000000000002
Returnability	Y
Country of origin	ID

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1547 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov